

8808250SBA Cut Sheet

KNIPEX Alligator adjustable pliers, 10.0in (254mm) overall length, insulated, 1000V insulation rating, cushion grip handles, finger pinch guard and serrated gripping surface.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/8808250SBA>

Technical Specifications

Brand	KNIPEX
Series	Alligator
Item	Pliers
Pliers Type	Adjustable
Overall Length	10.0in (254mm)
Insulated	Yes
Insulation Rating	1000V
Capacity	1-31/32in round or 1-13/16in hex

Handle Type	Cushion grip handles
Application	Gripping
Material	Chrome vanadium electric steel, forged, oil-hardened
Applicable Standards	DIN ISO 8976
Tool Features	Finger pinch guard and serrated gripping surface
Additional Information	9 adjustment positions for 30% more gripping capacity. ASTM F1505-tested

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document