

88257C1 Cut Sheet



Metal Work pneumatic threaded fitting, recessed hex plug, brass body, brass threads, Buna-N O-ring seal(s), G1/8 male BSPP.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/88257C1>

Technical Specifications

Brand	Metal Work
Item	Fitting
Working Fluid	Air or inert gas
Fitting Connection Type	Threaded
Fitting Type	Recessed hex plug
Body Material	Brass
Thread Material	Brass

Thread Sealant	No
Seal Material	Buna-N O-ring
Fitting Measurement Type	SAE
Connection	G1/8 male BSPP
Operating Pressure	232 psi
Operating Temperature	-4 to +176 °F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/88257C1.pdf>
See store item page for other formats.