

# 88MXL025NG Cut Sheet



SureMotion timing belt, 0.08in MXL pitch, 1/4in wide, 88 tooth, 7in pitch length (circumference), neoprene, fiberglass reinforced. Package of 3.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/88MXL025NG>

## Technical Specifications

Brand	SureMotion
Item	Timing belt
Pitch	0.08in MXL
Width	1/4in
Number of Teeth	88
Pitch length	7in
Material	Neoprene
Reinforcement	Fiberglass
Belt Tensile Rating	103lb
Quantity per Pack	3

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/88MXL025NG.pdf>  
See store item page for other formats.