



STAHL intrinsically safe Zener barrier, common usage: NPN sensors and dry contacts, 24 VDC operating voltage, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9002/11-280-186-001>

Technical Specifications

Brand	STAHL
Item	Barrier
Barrier Type	Zener
Intrinsically Safe	Yes
Barrier Common Usage	NPN sensors and dry contacts
Maximum Voltage	28 VDC
Maximum Current	186 mA
Maximum Power	1300 mW
Operating Voltage	24 VDC
Housing Material	Polyamide
Mounting	35mm DIN rail
Connection	Screw terminals
Application	Hazardous location rated

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	E81680
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/9002_11-280-186-001.pdf
See store item page for other formats.