



STAHL intrinsically safe Zener barrier, common usage: 4-wire RTD, 7.5 VDC operating voltage, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9002/77-093-040-001>

Technical Specifications

Brand	STAHL
Item	Barrier
Barrier Type	Zener
Intrinsically Safe	Yes
Barrier Common Usage	4-wire RTD
Maximum Voltage	9.3 VDC
Maximum Current	20 mA

Maximum Power	50 mW
Operating Voltage	7.5 VDC
Housing Material	Polyamide
Mounting	35mm DIN rail
Connection	Screw terminals
Application	Hazardous location rated

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	E81680
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	View FM Approval and UL Control Drawing

Dimensional Drawings



2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/9002_77-093-040-001.pdf
See store item page for other formats.