

9006060000 Cut Sheet



Weidmuller SWIFTY CS 3.5mm slotted standard cutting and stripping screwdriver, 3.9in (100mm) shaft length, cushion grip handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9006060000>

Technical Specifications

Brand	Weidmuller
Series	SWIFTY CS
Item	Cutting and stripping screwdriver
Screwdriver Type	Standard
Tip Type	Slotted
Tip Size	3.5mm
Slotted Tip Thickness	0.6mm
Insulated	No
Overall Length	8.0in (203mm)

Shaft Length	3.9in (100mm)
Shaft Diameter	0.14in (3.5mm)
Reduced Shank	No
Handle Length	4.1in (105mm)
Handle Type	Cushion grip handle
Application	Screwdriving, wire cutting and wire stripping
Tool Features	Integrated cutting and stripping on shaft
Additional Information	Includes SWIFTY cutting and stripping tool for one-hand screwdriving operation

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document