

9014350000 Cut Sheet



Weidmuller wire crimping tool, self-adjusting, rotatable die, trapezoidal profile, 26–10 AWG capacity, compatible with insulated and non-insulated wire ferrules.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9014350000>

Technical Specifications

| | |
|-----------------------------|---|
| Brand | Weidmuller |
| Item | Wire crimping tool |
| Self-adjusting | Yes |
| Rotatable Die | Yes |
| Crimp Profile | Trapezoidal |
| Crimp Length | 0.57in (14.5mm) |
| Capacity | 26–10 AWG |
| Compatible Connector | Insulated and non-insulated wire ferrules |
| Handle Type | Plastic coated handles |
| Overall Length | 7.9in (200mm) |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |