

9020000000 Cut Sheet



Weidmuller cutting, stripping, and crimping tool, self-adjusting, trapezoidal profile, 20-14 AWG capacity, compatible with insulated and non-insulated wire ferrules. For use with 9004320000, 9004270000, 9004290000, 9004360000, and 9004340000 wire ferrule strips.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9020000000>

Technical Specifications

Brand	Weidmuller
Item	Cutting, stripping, and crimping tool
Self-adjusting	Yes
Rotatable Die	No
Crimp Profile	Trapezoidal
Crimp Length	8.0mm/0.31in
Capacity	20-14 AWG
Compatible Connector	Insulated and non-insulated wire ferrules

Cutting	Beveled cutting edges
Handle Type	Comfort grip handles
Overall Length	8.2in (210mm)
For Use With	9004320000, 9004270000, 9004290000, 9004360000, and 9004340000 wire ferrule strips
Additional Information	Ferrule strips are stored in the tool and presented for each crimp

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document