

9020185 Cut Sheet



KNIPEX flexible hose and pvc pipe cutter, spring return single acting. For use with thin walled pipes and flexible hoses up to 1in (25.4mm) outside diameter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9020185>

Technical Specifications

Brand	KNIPEX
Item	Flexible hose and pvc pipe cutter
Action Type	Spring return single acting
Blade Type	Trapezoidal
Overall Length	7.3in
For Use With	Thin walled pipes and flexible hoses up to 1in (25.4mm) outside diameter
Additional Information	Cutting blades are replaceable

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement