

# 9041366U Cut Sheet



Metal Work pneumatic push-to-connect fitting, inline flow control valve, technopolymer body, (1) 1/4in push-to-connect to (1) 1/4in push-to-connect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9041366U>

## Technical Specifications

<b>Brand</b>	Metal Work
<b>Item</b>	Fitting
<b>Working Fluid</b>	Air or inert gas
<b>Fitting Connection Type</b>	Push-to-connect
<b>Fitting Type</b>	Inline flow control valve
<b>Body Material</b>	Technopolymer
<b>Thread Sealant</b>	No

<b>Fitting Measurement Type</b>	SAE
<b>Connection</b>	(1) 1/4in push-to-connect to (1) 1/4in push-to-connect
<b>Operating Pressure</b>	0-145 psi
<b>Operating Temperature</b>	-4 to +140 °F
<b>For Use With</b>	Flexible pneumatic tubing

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/9041366U.pdf>  
See store item page for other formats.