

9061332U Cut Sheet



Metal Work pneumatic push-to-connect fitting, inline pressure regulator, technopolymer body, (1) 3/8in push-to-connect inlet(s), (1) 3/8in push-to-connect outlet(s), 14.5–116 psi range.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9061332U>

Technical Specifications

| | |
|--------------------------------|---------------------------|
| Brand | Metal Work |
| Item | Fitting |
| Working Fluid | Air or inert gas |
| Fitting Connection Type | Push-to-connect |
| Fitting Type | Inline pressure regulator |
| Body Material | Technopolymer |

| | |
|---------------------------------|---------------------------|
| Thread Sealant | No |
| Fitting Measurement Type | SAE |
| Inlet Port | (1) 3/8in push-to-connect |
| Outlet Port | (1) 3/8in push-to-connect |
| Pressure Range | 14.5–116 psi |
| Operating Temperature | -4 to +140 °F |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/9061332U.pdf>
See store item page for other formats.