

9063116 Cut Sheet



Metal Work pneumatic push-to-connect fitting, inline quick exhaust valve, technopolymer body, (1) 6mm push-to-connect inlet(s), (1) 6mm push-to-connect outlet(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9063116>

Technical Specifications

Brand	Metal Work
Item	Fitting
Working Fluid	Air or inert gas
Fitting Connection Type	Push-to-connect
Fitting Type	Inline quick exhaust valve
Body Material	Technopolymer
Thread Sealant	No
Fitting Measurement Type	Metric
Inlet Port	(1) 6mm push-to-connect
Outlet Port	(1) 6mm push-to-connect
Operating Temperature	-4 to +140 °F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/9063116.pdf>
See store item page for other formats.