

9067616 Cut Sheet



Metal Work pneumatic push-to-connect fitting, pilot valve, 3-way N.C., technopolymer body, (2) 6mm push-to-connect to (1) 5/32in (4mm) push-to-connect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9067616>

Technical Specifications

Brand	Metal Work
Item	Fitting
Working Fluid	Air or inert gas
Fitting Connection Type	Push-to-connect
Fitting Type	Pilot valve
Valve Function	3-way N.C.
Body Material	Technopolymer

Thread Sealant	No
Fitting Measurement Type	Metric
Connection	(2) 6mm push-to-connect and (1) 5/32in (4mm) push-to-connect
Operating Pressure	0-145 psi
Operating Temperature	-4 to +140 °F
For Use With	Flexible pneumatic tubing

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/9067616.pdf>
See store item page for other formats.