

# 907.02003-PP000001 Cut Sheet



Ergoswiss SQ series spindle lifting column, 300mm stroke, 330 lbs/150 kg, 24 VAC, IP20, slot size 8. For use with 40 x 40mm and 1.5 x 1.5in profile T-slotted rails. (1) 6.5ft/2m power cable included. Requires Ergoswiss 124.43801-PP000001 control box.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/907.02003-PP000001>

## Technical Specifications

<b>Brand</b>	Ergoswiss	<b>Voltage Rating</b>	24 VAC
<b>Item</b>	Spindle lifting column	<b>IP Rating</b>	IP20
<b>Series</b>	SQ	<b>Slot Size</b>	8
<b>Stroke</b>	300mm	<b>Operating Temperature</b>	50 to 104 deg F
<b>Load Rating</b>	330 lbs/150 kg	<b>For Use With</b>	40 x 40mm and 1.5 x 1.5in profile T-slotted rails
<b>Lifting Speed</b>	9mm/sec	<b>Includes</b>	(1) 6.5ft/2m power cable
<b>Average Noise Level</b>	<60 dBA	<b>Requires</b>	Ergoswiss 124.43801-PP000001 control box

## Agency Approvals

<b>UL Listed File #</b>	E487840
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/907.02003-PP000001.pdf>  
See store item page for other formats.