

907.02004-PP000001 Cut Sheet



Ergoswiss SQ series spindle lifting column, 400mm stroke, 330 lbs/150 kg, 24 VAC, IP20, slot size 8. For use with 40 x 40mm and 1.5 x 1.5in profile T-slotted rails. (1) 6.5ft/2m power cable included. Requires Ergoswiss 124.43800-PP000001 control box.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/907.02004-PP000001>

Technical Specifications

Brand	Ergoswiss	Voltage Rating	24 VAC
Item	Spindle lifting column	IP Rating	IP20
Series	SQ	Slot Size	8
Stroke	400mm	Operating Temperature	50 to 104 deg F
Load Rating	330 lbs/150 kg	For Use With	40 x 40mm and 1.5 x 1.5in profile T-slotted rails
Lifting Speed	9mm/sec	Includes	(1) 6.5ft/2m power cable
Average Noise Level	<60 dBA	Requires	Ergoswiss 124.43800-PP000001 control box

Agency Approvals

UL Listed File #	E487840
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/907.02004-PP000001.pdf>
See store item page for other formats.