

9070132U Cut Sheet



Metal Work mechanical pressure switch, 7.5–145 psig set point, 5.8–11.6 psig deadband range, brass sensing element, nitrile seal(s), SPDT 2A, (2) 3/8in push-to-connect process connection, 1ft/0.3m cable with 3-pin M8 snap-fit connector.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9070132U>

Technical Specifications

Brand	Metal Work
Item	Mechanical pressure switch
Media Type	Air
Setpoint Range	7.5–145 psig
Deadband Range	5.8–11.6 psig
Actuator Type	Metal pin plunger
Wetted Parts	Technopolymer, brass, nitrile

Sensing Element Material	Brass
Seal Material	Nitrile
Switching Output	SPDT 2A
Process Connection	(2) 3/8in push-to-connect
IP Rating	IP65
Electrical Connection	1ft/0.3m cable with 3-pin M8 snap-fit connector

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/9070132U.pdf>
See store item page for other formats.