

908090 Cut Sheet



Dehn DG-SU series power Surge Protective Device (SPD), 20 kA discharge current, 120 VAC 1-Phase, parallel circuit, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/908090>

Technical Specifications

Brand	Dehn
Item	Surge Protective Device (SPD)
Series	DG-SU
Surge Protection Type	Power protection
UL Type	UL Type 1
Circuit Type	Parallel circuit
Neutral Ground Protection	No
System Voltage	120 VAC 1-Phase
Nominal Discharge Current	20 kA
Voltage Protection Rating (VPR)	700V (L-L)
Per Phase Max Surge Capacity	50 kA
Indicating Type	Red/green indicating flag
SCCR Rating	200kA SCCR
UL Rating	UL 1449 rated
Mounting	35mm DIN rail
Connection	Screw terminal
Includes	(1) SPDT health status contact

Agency Approvals

UL Listed File #	E319777
UL Hazardous File #	None
CE	None
CSA File #	215727
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document