

# 908090 Cut Sheet



Dehn DG-SU series power Surge Protective Device (SPD), 20 kA discharge current, 120 VAC 1-Phase, parallel circuit, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/908090>

## Technical Specifications

Brand	Dehn
Item	Surge Protective Device (SPD)
Series	DG-SU
Surge Protection Type	Power protection
UL Type	UL Type 1
Circuit Type	Parallel circuit
Neutral Ground Protection	No
System Voltage	120 VAC 1-Phase
Nominal Discharge Current	20 kA
Voltage Protection Rating (VPR)	700V (L-L)

Per Phase Max Surge Capacity	50 kA
Indicating Type	Red/green indicating flag
SCCR Rating	200kA SCCR
UL Rating	UL 1449 rated
Mounting	35mm DIN rail
Connection	Screw terminal
Includes	(1) SPDT health status contact

## Agency Approvals

UL Listed File #	E319777
UL Hazardous File #	None
CE	None
CSA File #	215727
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/908090.pdf>  
See store item page for other formats.