

# 908345 Cut Sheet



Dehn DG-MU series power Surge Protective Device (SPD), 20 kA discharge current, 208/120 VAC 3-Phase Wye, neutral ground protection, parallel circuit, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/908345>

## Technical Specifications

|  |  |
|--|--|
| <b>Brand</b>                           | Dehn   |
| <b>Item</b>                            | Surge Protective Device (SPD)                    |
| <b>Series</b>                          | DG-MU  |
| <b>Surge Protection Type</b>           | Power protection                                 |
| <b>UL Type</b>                         | UL Type 1  |
| <b>Circuit Type</b>                    | Parallel circuit                                 |
| <b>Neutral Ground Protection</b>       | Yes  |
| <b>System Voltage</b>                  | 208/120 VAC 3-Phase Wye                          |
| <b>Nominal Discharge Current</b>       | 20 kA  |
| <b>Voltage Protection Rating (VPR)</b> | 1200V (L-L), 1200V (L-G), 600V (L-N), 600V (N-G) |

|                                     |                                |
|-------------------------------------|--------------------------------|
| <b>Per Phase Max Surge Capacity</b> | 50 kA                          |
| <b>Indicating Type</b>              | Red/green indicating flag      |
| <b>SCCR Rating</b>                  | 200kA SCCR                     |
| <b>UL Rating</b>                    | UL 1449 rated                  |
| <b>Mounting</b>                     | 35mm DIN rail                  |
| <b>Connection</b>                   | Screw terminal                 |
| <b>Includes</b>                     | (1) SPDT health status contact |

## Agency Approvals

|                            |  |
|----------------------------|--|
| <b>UL Listed File #</b>    | E319777                                |
| <b>UL Hazardous File #</b> | None                                   |
| <b>CE</b>                  | None                                   |
| <b>CSA File #</b>          | 215727                                 |
| <b>RoHS Status</b>         | No                                     |
| <b>EU REACH</b>            | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/908345.pdf>  
See store item page for other formats.