

908346 Cut Sheet



Dehn DG-MU series power Surge Protective Device (SPD), 20 kA discharge current, 480/277 VAC 3-Phase Wye, neutral ground protection, parallel circuit, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/908346>

Technical Specifications

Brand	Dehn
Item	Surge Protective Device (SPD)
Series	DG-MU
Surge Protection Type	Power protection
UL Type	UL Type 1
Circuit Type	Parallel circuit
Neutral Ground Protection	Yes
System Voltage	480/277 VAC 3-Phase Wye
Nominal Discharge Current	20 kA
Voltage Protection Rating (VPR)	2500V (L-L), 1800V (L-G), 1200V (L-N), 600V (N-G)
Per Phase Max Surge Capacity	50 kA
Indicating Type	Red/green indicating flag
SCCR Rating	200kA SCCR
UL Rating	UL 1449 rated
Mounting	35mm DIN rail
Connection	Screw terminal
Includes	(1) SPDT health status contact

Agency Approvals

UL Listed File #	E319777
UL Hazardous File #	None
CE	None
CSA File #	215727
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document