

908347 Cut Sheet



Dehn DG-MU series power Surge Protective Device (SPD), 20 kA discharge current, 600/347 VAC 3-Phase Wye, neutral ground protection, parallel circuit, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/908347>

Technical Specifications

Brand	Dehn	Voltage Protection Rating (VPR)	3000V (L-L), 2000V (L-G), 1500V (L-N), 600V (N-G)
Item	Surge Protective Device (SPD)	Per Phase Max Surge Capacity	50 kA
Series	DG-MU	Indicating Type	Red/green indicating flag
Surge Protection Type	Power protection	SCCR Rating	200kA SCCR
UL Type	UL Type 1	UL Rating	UL 1449 rated
Circuit Type	Parallel circuit	Mounting	35mm DIN rail
Neutral Ground Protection	Yes	Connection	Screw terminal
System Voltage	600/347 VAC 3-Phase Wye	Includes	(1) SPDT health status contact
Nominal Discharge Current	20 kA		

Agency Approvals

UL Listed File #	E319777
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	215727
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/908347.pdf>
See store item page for other formats.