

# 908355 Cut Sheet



Dehn DG-MU series power Surge Protective Device (SPD), 20 kA discharge current, 480 VAC 3-Phase Delta, parallel circuit, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/908355>

## Technical Specifications

<b>Brand</b>	Dehn
<b>Item</b>	Surge Protective Device (SPD)
<b>Series</b>	DG-MU
<b>Surge Protection Type</b>	Power protection
<b>UL Type</b>	UL Type 1
<b>Circuit Type</b>	Parallel circuit
<b>Neutral Ground Protection</b>	No
<b>System Voltage</b>	480 VAC 3-Phase Delta
<b>Nominal Discharge Current</b>	20 kA
<b>Voltage Protection Rating (VPR)</b>	3000V (L-L), 1800V (L-G)
<b>Per Phase Max Surge Capacity</b>	50 kA
<b>Indicating Type</b>	Red/green indicating flag
<b>SCCR Rating</b>	200kA SCCR
<b>UL Rating</b>	UL 1449 rated
<b>Mounting</b>	35mm DIN rail
<b>Connection</b>	Screw terminal
<b>Includes</b>	(1) SPDT health status contact

## Agency Approvals

<b>UL Listed File #</b>	E319777
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	215727
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>