

# 908 Cut Sheet



CHANNELLOCK multi-purpose wiring tool, compatible with data & communications cable and round wire, precision machined hardened cutting edges, 22-12 AWG stranded and 20-10 AWG solid wire stripping capacity, 10 AWG cutting capacity.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/908>

## Technical Specifications

Brand	CHANNELLOCK
Item	Wiring tool
Stripper Type	Multi-purpose
Compatible Wire/Cable	Data & communications cable and round wire
Compatible Connector	Insulated and non-insulated terminals and connectors
Overall Length	8.0in (203mm)
Cutting	Precision machined hardened cutting edges

Self-adjusting	No
Wire Stripping Capacity	22-12 AWG stranded and 20-10 AWG solid
Cutting Capacity	10 AWG
Application	Wire stripping, wire cutting, crimping and bolt cutting
Tool Features	Integrated screw shears (10-24, 6-32, 8-32, 10-32, 4-40) and lean nose for pulling and looping wire

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>