909 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

CHANNELLOCK crimping pliers, multiple profile, 22–10 AWG capacity, compatible with insulated and non-insulated terminals and connectors.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/909

Technical Specifications

Brand	CHANNELLOCK
Item	Crimping pliers
Self-adjusting	No
Rotatable Die	No
Crimp Profile	Multiple
Crimp Length	12mm/0.47in
Capacity	22–10 AWG
Compatible Connector	Insulated and non-insulated terminals and connectors
Cutting	Induction hardened beveled cutting edges
Handle Type	Classic grip vinyl handles
Overall Length	9.5in (241mm)
Material	High carbon steel (HCS)

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document