

# 91005B Cut Sheet



Halex fitting, zinc die cast, 90-degree, 1/2in trade size, screw clamp conduit connection, insulation. Package of 25. For use with flexible metal conduit (FMC), AC cable (BX), MC cable. Screws and locknut included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/91005B>

## Technical Specifications

<b>Brand</b>	Halex	<b>Flexible Metal Conduit (FMC) Compatibility</b>	Aluminum FMC, aluminum RWFMC, aluminum XRWFC, steel FMC, steel RWFMC and steel XRWFC
<b>Item</b>	Fitting	<b>Armored Cable (AC) Size Range</b>	Aluminum 10/4-6/4 and steel 10/4-8/3
<b>Liquid-tight</b>	No	<b>Metal Clad (MC) Cable Size Range</b>	Aluminum 10/4-6/4 and steel 10/4-6/3
<b>Fitting Type</b>	90-degree	<b>Quantity per Pack</b>	25
<b>Material</b>	Zinc die cast	<b>For Use With</b>	Flexible metal conduit (FMC), AC cable (BX), MC cable
<b>Trade Size</b>	1/2in	<b>Includes</b>	Screws and locknut
<b>Conduit Connection Method</b>	Screw clamp	<b>Applicable Standards</b>	UL 514B Listed
<b>Box Connection Type</b>	1/2in male NPSM		
<b>Insulation</b>	Yes		
<b>Knockout Size</b>	1/2in		
<b>Reduced Wall Flexible Metal Conduit Trade Size</b>	1/2in		

## Agency Approvals

<b>UL Listed File #</b>	E30248
<b>CE</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>