

91007B Cut Sheet



Halex fitting, zinc die cast, 90-degree, 3/4in trade size, screw clamp conduit connection, insulation. Package of 10. For use with flexible metal conduit (FMC), AC cable (BX), MC cable. Screws and locknut included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/91007B>

Technical Specifications

Brand	Halex	Flexible Metal Conduit (FMC) Compatibility	Aluminum FMC, aluminum RWFC, steel FMC, steel RWFC and steel XRWFC
Item	Fitting	Armored Cable (AC) Size Range	Aluminum 6/4-2/4 and steel 6/4-3/4
Liquid-tight	No	Metal Clad (MC) Cable Size Range	Aluminum 8/4-3/4 and steel 8/4-3/4
Fitting Type	90-degree	Quantity per Pack	10
Material	Zinc die cast	For Use With	Flexible metal conduit (FMC), AC cable (BX), MC cable
Trade Size	3/4in	Includes	Screws and locknut
Conduit Connection Method	Screw clamp	Applicable Standards	UL 514B Listed
Box Connection Type	3/4in male NPSM		
Insulation	Yes		
Knockout Size	3/4in		
Reduced Wall Flexible Metal Conduit Trade Size	3/4in		

Agency Approvals

UL Listed File #	E30248
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement