

# 91010B Cut Sheet



Halex fitting, zinc die cast, 90-degree, 1in trade size, screw clamp conduit connection, insulation. Package of 1. For use with flexible metal conduit (FMC), AC cable (BX), MC cable. Screws and locknut included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/91010B>

## Technical Specifications

<b>Brand</b>	Halex	<b>Flexible Metal Conduit (FMC) Compatibility</b>	Aluminum FMC, aluminum RWFC, steel FMC and steel RWFC
<b>Item</b>	Fitting	<b>Armored Cable (AC) Size Range</b>	Aluminum 4/3-2/4 and steel 3/4-2/4
<b>Liquid-tight</b>	No	<b>Metal Clad (MC) Cable Size Range</b>	Aluminum 3/4-1/3 and steel 3/4-0/3
<b>Fitting Type</b>	90-degree	<b>Quantity per Pack</b>	1
<b>Material</b>	Zinc die cast	<b>For Use With</b>	Flexible metal conduit (FMC), AC cable (BX), MC cable
<b>Trade Size</b>	1in	<b>Includes</b>	Screws and locknut
<b>Conduit Connection Method</b>	Screw clamp	<b>Applicable Standards</b>	UL 514B Listed
<b>Box Connection Type</b>	1in male NPSM		
<b>Insulation</b>	Yes		
<b>Knockout Size</b>	1in		
<b>Reduced Wall Flexible Metal Conduit Trade Size</b>	1in		

## Agency Approvals

<b>UL Listed File #</b>	E30248
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>