

9146-20-11-11S Cut Sheet



STAHL intrinsically safe frequency transmitter isolator, (2) 0.001 Hz to 20 kHz input, (2) 0-20 mA or (2) 4-20 mA output, 24 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9146-20-11-11S>

Technical Specifications

Brand	STAHL
Item	Isolator
Isolator Type	Frequency transmitter
Intrinsically Safe	Yes
Input	(2) 0.001 Hz to 20 kHz
Output	(2) 0-20 mA or (2) 4-20 mA
Maximum Voltage	10.5 VDC
Maximum Current	23.4 mA
Maximum Power	61.4 mW
Operating Voltage	24 VDC
Housing Material	Polyamide
Mounting	35mm DIN rail
Connection	Screw terminals
Application	Hazardous location rated
Additional Information	Manufacturer part number: 9146/20-11-11s

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	FM Approval