

9260-13-11-10S Cut Sheet



STAHL intrinsically safe analog input isolator, 0-20 mA or 4-20 mA input, 0-20 mA or 4-20 mA output, 24 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9260-13-11-10S>

Technical Specifications

Brand	STAHL
Item	Isolator
Isolator Type	Analog input
Intrinsically Safe	Yes
Input	0-20 mA or 4-20 mA
Output	0-20 mA or 4-20 mA
Maximum Voltage	25.2 VDC
Maximum Current	93 mA
Maximum Power	587 mW
Operating Voltage	24 VDC
Housing Material	Polyamide
Mounting	35mm DIN rail
Connection	Screw terminals
Application	Hazardous location rated
Additional Information	Manufacturer part number: 9260/13-11-10s

Agency Approvals

UL Listed File #	E81680
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document