

9511160SBA Cut Sheet



KNIPEX StepCut cable shears, 6.3in (159mm) overall length, induction hardened shear cutting edges, plastic coated handles, finger pinch guard.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9511160SBA>

Technical Specifications

Brand	KNIPEX
Series	StepCut
Item	Cable shears
Overall Length	6.3in (159mm)
Cutting	Induction hardened shear cutting edges
Capacity	1/0 AWG stranded
Handle Type	Plastic coated handles
Application	Wire cutting and cable cutting

Material	High-grade special tool steel, forged, oil-hardened
Tool Features	Finger pinch guard
Additional Information	Cutting edge gradations cut wires one after the other making cutting 40% easier than with standard cable shears of the same length. Not suitable for steel wire and hard drawn copper conductors

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement