

9511200SBA Cut Sheet



KNIPEX cable shears, 8.0in (203mm) overall length, induction hardened shear cutting edges, plastic coated handles, finger pinch guard and twin cutting edge.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9511200SBA>

Technical Specifications

| | |
|-------------------------------|--|
| Brand | KNIPEX |
| Item | Cable shears |
| Overall Length | 8.0in (203mm) |
| Insulated | No |
| Cutting | Induction hardened shear cutting edges |
| Capacity | 2/0 AWG stranded |
| Handle Type | Plastic coated handles |
| Application | Wire cutting and cable cutting |
| Material | High-grade special tool steel, forged, oil-hardened |
| Tool Features | Finger pinch guard and twin cutting edge |
| Additional Information | Not suitable for steel wire and hard drawn copper conductors |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |