

9516165T Cut Sheet



KNIPEX cable shears, 6.5in (165mm) overall length, insulated, 1000V insulation rating, induction hardened shear cutting edges, insulated cushion grip handles, finger pinch guard and tether attachment point.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9516165T>

Technical Specifications

Brand	KNIPEX
Item	Cable shears
Overall Length	6.5in (165mm)
Insulated	Yes
Insulation Rating	1000V
Cutting	Induction hardened shear cutting edges
Capacity	19/32in round

Handle Type	Insulated cushion grip handles
Application	Wire cutting and cable cutting
Material	Chrome vanadium electric steel, forged, oil-hardened
Tool Features	Finger pinch guard and tether attachment point
Additional Information	Not suitable for steel wire and hard drawn copper conductors. VDE-tested

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement