

9530NP Cut Sheet



Bryant industrial heavy duty straight blade plug, 30A, 125 VAC, 1-phase, 2-pole, 3-wire, NEMA 5-30, accepts cord size 0.42-1.32in, thermoplastic housing, gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9530NP>

Technical Specifications

Brand	Bryant
Item	Plug
Application	Industrial heavy duty
Blade Type	Straight
With Cap	No
Self-grounding	No
Amperage Rating	30A
Voltage Rating	125 VAC
Number of Phases	1
Number of Poles	2
Number of Wires	3
Wire Size	18-10 AWG
Copper Wire Only	No
Configuration	NEMA 5-30
Cord Diameter	0.42-1.32in
Housing Material	Thermoplastic
Color	Gray

Agency Approvals

UL Listed File #	E1381
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	016215
RoHS Status	No
EU REACH	View EU REACH document