

9531250SBA Cut Sheet

KNIPEX cable shears, 10.0in (254mm) overall length, multi-component soft grip, finger pinch guard and two stage ratchet drive.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9531250SBA>

Technical Specifications

Brand	KNIPEX
Item	Cable shears
Overall Length	10.0in (254mm)
Insulated	No
Capacity	1-1/4in (500kcmil)
Handle Type	Multi-component soft grip
Application	Wire cutting and cable cutting
Material	High-grade special tool steel, forged, oil-hardened
Tool Features	Finger pinch guard and two stage ratchet drive
Additional Information	Not suitable for steel wire and wire ropes

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document