

957 Cut Sheet



CHANNELLOCK multi-purpose wiring tool, compatible with data & communications cable and round wire, precision machined hardened cutting edges, 20–12 AWG stranded and 18–10 AWG solid wire stripping capacity, 10 AWG cutting capacity.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/957>

Technical Specifications

Brand	CHANNELLOCK
Item	Wiring tool
Stripper Type	Multi-purpose
Compatible Wire/Cable	Data & communications cable and round wire
Overall Length	7.0in (177mm)
Cutting	Precision machined hardened cutting edges
Self-adjusting	No
Wire Stripping Capacity	20–12 AWG stranded and 18–10 AWG solid
Cutting Capacity	10 AWG
Application	Wire stripping, wire cutting and bolt cutting
Tool Features	Integrated screw shears (6-32, 8-32) and lean nose for pulling and looping wire

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document