

# 96200010 Cut Sheet



LS Electric high-precision planetary gearbox, 5:1 ratio, inline, 32mm diameter output shaft, nominal output torque 332 N-m (2939 lb-in), 1-stage, 115mm frame. For use with APM-FE series 2.2 kW motors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/96200010>

## Technical Specifications

Brand	LS Electric
Item	Gearbox
Application	High-precision
Gearbox Type	Planetary
Gear Ratio	5:1
Output Configuration	Inline
Gearbox Output Shaft Diameter	32mm

Nominal Output Torque	Nominal output torque 332 N-m (2939 lb-in)
Number of Stages	1
Frame	115mm
For Use With	APM-FE series 2.2 kW motors
Includes	Input adapter bushing, motor mounting hardware and output shaft key
Manufacturer Part Number	MSS1151A-005KS-D3110103C24

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	RoHS Statement

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/96200010.pdf>  
See store item page for other formats.