

96200103 Cut Sheet



LS Electric high-precision planetary gearbox, 20:1 ratio, inline, 22mm diameter output shaft, nominal output torque 143 N-m (1266 lb-in), 2-stage, 90mm frame. For use with FBL series 100W-400W motors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/96200103>

Technical Specifications

Brand	LS Electric
Item	Gearbox
Application	High-precision
Gearbox Type	Planetary
Gear Ratio	20:1
Output Configuration	Inline
Gearbox Output Shaft Diameter	22mm

Nominal Output Torque	Nominal output torque 143 N-m (1266 lb-in)
Number of Stages	2
Frame	90mm
For Use With	FBL series 100W, 200W and 400W motors
Includes	Input adapter bushing, motor mounting hardware and output shaft key
Manufacturer Part Number	MSS0902B-020KS-B3110103C14

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/96200103.pdf>
See store item page for other formats.