

96200479 Cut Sheet



LS Electric high-precision planetary gearbox, 20:1 ratio, inline, 40mm diameter output shaft, nominal output torque 295 N-m (2611 lb-in), 2-stage, 142mm frame. For use with APM-FE series 1.6 kW motors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/96200479>

Technical Specifications

Brand	LS Electric
Item	Gearbox
Application	High-precision
Gearbox Type	Planetary
Gear Ratio	20:1
Output Configuration	Inline
Gearbox Output Shaft Diameter	40mm

Nominal Output Torque	Nominal output torque 295 N-m (2611 lb-in)
Number of Stages	2
Frame	142mm
For Use With	APM-FE series 1.6 kW motors
Includes	Input adapter bushing, motor mounting hardware and output shaft key
Manufacturer Part Number	MSS1422B-020KS-D3110103C22

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/96200479.pdf>
See store item page for other formats.