

96200862 Cut Sheet



LS Electric high-precision planetary gearbox, 15:1 ratio, inline, 55mm diameter output shaft, nominal output torque 897 N-m (7939 lb-in), 2-stage, 180mm frame. For use with APM-FF series 7.5 kW motors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/96200862>

Technical Specifications

Brand	LS Electric
Item	Gearbox
Application	High-precision
Gearbox Type	Planetary
Gear Ratio	15:1
Output Configuration	Inline
Gearbox Output Shaft Diameter	55mm
Nominal Output Torque	Nominal output torque 897 N-m (7939 lb-in)
Number of Stages	2
Frame	180mm
For Use With	APM-FF series 7.5 kW motors
Includes	Input adapter bushing, motor mounting hardware and output shaft key
Manufacturer Part Number	MSS1802A-015KS-F3110103C42

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement