

# 9630FR Cut Sheet



Bryant industrial heavy duty single straight blade receptacle, 30A, 250 VAC, 1-phase, 2-pole, 3-wire, NEMA 6-30, thermoplastic molded housing, gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/9630FR>

## Technical Specifications

Brand	Bryant
Item	Receptacle
Application	Industrial heavy duty
Receptacle Type	Single
Blade Type	Straight
With Cap	No
Self-grounding	No
Amperage Rating	30A
Voltage Rating	250 VAC

Number of Phases	1
Number of Poles	2
Number of Wires	3
Wire Size	14-8 AWG solid or stranded
Copper Wire Only	Yes
Configuration	NEMA 6-30
Housing Material	Thermoplastic molded
Color	Gray

## Agency Approvals

UL Listed File #	E2258
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	016215
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/9630FR.pdf>  
See store item page for other formats.