

# 968 Cut Sheet



CHANNELLOCK multi-purpose wiring tool, compatible with data & communications cable and round wire, comfort grip, curved shear cutting edges, 20-12 AWG stranded and 18-10 AWG solid wire stripping capacity, 10 AWG cutting capacity.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/968>

## Technical Specifications

Brand	CHANNELLOCK
Item	Wiring tool
Stripper Type	Multi-purpose
Compatible Wire/Cable	Data & communications cable and round wire
Overall Length	7.5in (190mm)
Grip Type	Comfort grip
Cutting	Curved shear cutting edges
Self-adjusting	No
Wire Stripping Capacity	20-12 AWG stranded and 18-10 AWG solid
Cutting Capacity	10 AWG
Application	Wire stripping, wire cutting, deburring, reaming and bolt cutting
Tool Features	Integrated screw shears (6-32, 8-32) and 1in conduit reamer and deburrer

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>