

A-FJUI-11-08 Cut Sheet



igus drylin R series plain bearing, type J polymer bearing, 1/2in inside diameter, 1-11/16in overall length, fixed housing, 4-bolt flange pillow block, anodized aluminum, flanged.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A-FJUI-11-08>

Technical Specifications

Brand	igus
Item	Plain bearing
Series	Drylin R
Bearing Material	Type J polymer
Bearing Inside Diameter	1/2in
Overall Length	1-11/16in
Housing Fit	Fixed
Housing Type	4-bolt flange pillow block
Housing Material	Anodized aluminum
Housing Outside Diameter	1-1/4in
Flanged	Yes
Square Flange Dimension	1-5/8in

Agency Approvals

CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document