

# A-FJUI-11-12 Cut Sheet



igus drylin R series plain bearing, type J polymer bearing, 3/4in inside diameter, 2-1/16in overall length, fixed housing, 4-bolt flange pillow block, anodized aluminum, flanged.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A-FJUI-11-12>

## Technical Specifications

Brand	igus
Item	Plain bearing
Series	Drylin R
Bearing Material	Type J polymer
Bearing Inside Diameter	3/4in
Overall Length	2-1/16in
Housing Fit	Fixed
Housing Type	4-bolt flange pillow block
Housing Material	Anodized aluminum
Housing Outside Diameter	1-3/4in
Flanged	Yes
Square Flange Dimension	2-3/8in

## Agency Approvals

CE	<a href="#">View CE declarations</a>
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/A-FJUI-11-12.pdf>  
See store item page for other formats.