

A-FJUI-11-12 Cut Sheet



igus drylin R series plain bearing, type J polymer bearing, 3/4in inside diameter, 2-1/16in overall length, fixed housing, 4-bolt flange pillow block, anodized aluminum, flanged.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A-FJUI-11-12>

Technical Specifications

| | |
|--------------------------|----------------------------|
| Brand | igus |
| Item | Plain bearing |
| Series | Drylin R |
| Bearing Material | Type J polymer |
| Bearing Inside Diameter | 3/4in |
| Overall Length | 2-1/16in |
| Housing Fit | Fixed |
| Housing Type | 4-bolt flange pillow block |
| Housing Material | Anodized aluminum |
| Housing Outside Diameter | 1-3/4in |
| Flanged | Yes |
| Square Flange Dimension | 2-3/8in |

Agency Approvals

| | |
|-------------|----------------------------------------|
| CE | View CE declarations |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |