

A-FJUI-13-12 Cut Sheet



igus drylin R series plain bearing, type J polymer bearing, 3/4in inside diameter, 2-1/16in overall length, self-aligning housing, 4-bolt flange pillow block, anodized aluminum, flanged.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A-FJUI-13-12>

Technical Specifications

Brand	igus
Item	Plain bearing
Series	Drylin R
Bearing Material	Type J polymer
Bearing Inside Diameter	3/4in
Overall Length	2-1/16in
Housing Fit	Self-aligning
Housing Type	4-bolt flange pillow block
Housing Material	Anodized aluminum
Housing Outside Diameter	1-3/4in
Flanged	Yes
Square Flange Dimension	2-3/8in

Agency Approvals

CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/A-FJUI-13-12.pdf>
See store item page for other formats.