

A-GFI-0809-08 Cut Sheet



igus iglide series plain bearing, type G300 polymer, 1/2in inside diameter, 9/16in outside diameter, 1/2in overall length, flanged. Package of 10. For use with 1/2in diameter drylin R series shafts.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A-GFI-0809-08>

Technical Specifications

Brand	igus
Item	Plain bearing
Series	Iglide
Bearing Material	Type G300 polymer
Bearing Inside Diameter	1/2in
Bearing Outside Diameter	9/16in
Overall Length	1/2in
Flanged	Yes
Flange Outside Diameter	7/8in
Quantity per Pack	10
For Use With	1/2in diameter drylin R series shafts
Application	General purpose

Agency Approvals

CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/A-GFI-0809-08.pdf>
See store item page for other formats.