

A-OJUI-01-12 Cut Sheet



igus drylin R series plain bearing, type J polymer bearing, 3/4in inside diameter, 1-5/8in overall length, fixed housing, open, anodized aluminum.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A-OJUI-01-12>

Technical Specifications

| | |
|---------------------------------|-------------------|
| Brand | igus |
| Item | Plain bearing |
| Series | Drylin R |
| Bearing Material | Type J polymer |
| Bearing Inside Diameter | 3/4in |
| Overall Length | 1-5/8in |
| Housing Fit | Fixed |
| Housing Type | Open |
| Housing Material | Anodized aluminum |
| Housing Outside Diameter | 1-1/4in |
| Flanged | No |

Agency Approvals

| | |
|--------------------|--|
| CE | View CE declarations |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/A-OJUI-01-12.pdf>
See store item page for other formats.