

# A-RJI-01-12 Cut Sheet



igus drylin R series plain bearing, type J polymer bearing, 3/4in inside diameter, 1-5/8in overall length, fixed housing, closed, type J polymer.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A-RJI-01-12>

## Technical Specifications

|                                 |                |
|---------------------------------|----------------|
| <b>Brand</b>                    | igus           |
| <b>Item</b>                     | Plain bearing  |
| <b>Series</b>                   | Drylin R       |
| <b>Bearing Material</b>         | Type J polymer |
| <b>Bearing Inside Diameter</b>  | 3/4in          |
| <b>Overall Length</b>           | 1-5/8in        |
| <b>Housing Fit</b>              | Fixed          |
| <b>Housing Type</b>             | Closed         |
| <b>Housing Material</b>         | Type J polymer |
| <b>Housing Outside Diameter</b> | 1-1/4in        |
| <b>Flanged</b>                  | No             |

## Agency Approvals

|                    |  |
|--------------------|--|
| <b>CE</b>          | <a href="#">View CE declarations</a>   |
| <b>RoHS Status</b> | Yes (See CE Doc)                       |
| <b>EU REACH</b>    | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/A-RJI-01-12.pdf>  
See store item page for other formats.