

# A-TFI-1214-12 Cut Sheet



igus iglide series plain bearing, type T500 polymer, 3/4in inside diameter, 7/8in outside diameter, 3/4in overall length, flanged. Package of 2. For use with 3/4in diameter drylin R series shafts.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A-TFI-1214-12>

---

## Technical Specifications

<b>Brand</b>	igus
<b>Item</b>	Plain bearing
<b>Series</b>	Iglide
<b>Bearing Material</b>	Type T500 polymer
<b>Bearing Inside Diameter</b>	3/4in
<b>Bearing Outside Diameter</b>	7/8in
<b>Overall Length</b>	3/4in
<b>Flanged</b>	Yes
<b>Flange Outside Diameter</b>	1-1/8in
<b>Quantity per Pack</b>	2
<b>For Use With</b>	3/4in diameter drylin R series shafts
<b>Application</b>	Chemical resistant, high temperatures

---

## Agency Approvals

<b>CE</b>	<a href="#">View CE declarations</a>
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>