

A-TSI-1214-12 Cut Sheet



igus iglide series plain bearing, type T500 polymer, 3/4in inside diameter, 7/8in outside diameter, 3/4in overall length. Package of 2. For use with 3/4in diameter drylin R series shafts.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A-TSI-1214-12>

Technical Specifications

| | |
|---------------------------------|---------------------------------------|
| Brand | igus |
| Item | Plain bearing |
| Series | Iglide |
| Bearing Material | Type T500 polymer |
| Bearing Inside Diameter | 3/4in |
| Bearing Outside Diameter | 7/8in |
| Overall Length | 3/4in |
| Flanged | No |
| Quantity per Pack | 2 |
| For Use With | 3/4in diameter drylin R series shafts |
| Application | Chemical resistant, high temperatures |

Agency Approvals

| | |
|--------------------|--|
| CE | View CE declarations |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |